

Oral-Liquid Filling Machine HHGL



Using in the filling sealing machine of oral liquid production line, can be used for filling, covering, sealing and filling of the cylinder. It adopts peristaltic pump filling, electromagnetic oscillation with cover, three-blade centrifugal seal (or screw cap), with no bottle filling function. The filling and sealing of this machine are two in one, with advanced design.

Technical Parameters:

Bottles applicability	10-30ml
Outout	80-100 bottles/minute
Power source	220V 50Hz
Power	1kw
Weight	800kg
Overall size	1600 x 1400 x 1600mm