

## Rotary Granulator ZL-series



ZL rotary granulator can press the mixed substances into the demanded particles. It is especially suitable for material of higher viscosity. Jincheng rotary granulator applies to industry such as pharmacy, chemical industry, tiny damp power material is ground pushing against Cheng expecting that the also may crush useless movie and dry piece and roller push against becoming a pellet.

Passing mechanical drive makes the roller knife and pressure expect that the leaf assumes appearance to revolution, pressure expects that certain Ye Cheng angle messenger material presses on downward entering the roller knife, grind the upper important knife angle helix leaf that material is pushed to griddle tube wall, still by the bit, with material are forced out from the sieve pore but able pellet.

### Technical Specifications:

Model	ZL-150-G	ZL-250-G	ZL-350-G
Motor Power(KW)	1.5	3	4
Bucket Dia.(mm)	150	250	350
Working Capacity(kg/h)	50-100	300-400	400-600
Production Time	continuity	continuity	continuity
Granule Dia.(mm)	1.2-3	1.2-3	1.2-3
Grind knives Speed(r/min)	60	50	36
Overall Size(mm)	700×400×700	1200×700×1100	1350×800×1200
Net Weight(kg)	120	400	600